



Boring bar blank Form A, SK 40, A dimension: 250mm



Order data

Order number	301301 250
GTIN	4062406105020
Item class	32A

Description

Version:

Taper arbor and collar hardened and ground.

Material:

16 MnCr5

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	250 mm
External \varnothing D	63 mm
Clamping \varnothing D ₁	63 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	A
Type of product	Boring bar blank

Accessories

Pull stud 90°sealed suitable for steep tapers 40	308790 40
--	-----------

ER chuck key 1/2 inch socket for ER collet chuck 40	309700 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
ER chuck key for ER collet chuck 40	309680 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studsealed suitable for steep tapers 40	308635 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Torque wrenchwith reversible ratchet maximum torque 200 N·m	656050 200
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studsealed, form B suitable for steep tapers 40	308650 40

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40

308801 40

Pull studsealed suitable for steep tapers 40

308660 40