

**Boring bar blank Form A, SK 50, A dimension: 315mm****Order data**

| | |
|--------------|---------------|
| Order number | 301302 315 |
| GTIN | 4062406105037 |
| Item class | 32A |

Description**Version:**

Taper arbor and collar hardened and ground.

Material:

16 MnCr5

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

| | |
|---------------------------------------|------------------|
| Overhang dimension A | 315 mm |
| External \varnothing D | 97 mm |
| Clamping \varnothing D ₁ | 97 mm |
| Adapter | SK 50 |
| Arbor standard | ISO 7388-1 |
| Shape | A |
| Type of product | Boring bar blank |

Accessories

308720 50

Special pull stud with no internal threadsealed suitable for steep tapers 50

| | |
|---|------------|
| Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50 | 308820 50 |
| Pull stud, 18CrNiMo7Form A suitable for steep tapers 50 | 308605 50 |
| Pull studsealed suitable for steep tapers 50 | 308660 50 |
| Pull studsealed, form B suitable for steep tapers 50 | 308620 50 |
| Pull stud 90°sealed suitable for steep tapers 50 | 308790 50 |
| Pull stud 45°sealed suitable for steep tapers 50 | 308760 50 |
| Pull stud 45°sealed suitable for steep tapers 50 | 308765 50 |
| Pull studsealed, form B suitable for steep tapers 50 | 308650 50 |
| Torque wrenchwith reversible ratchet maximum torque 200 N·m | 656050 200 |
| Pull studsealed, form A suitable for steep tapers 50 | 308610 50 |
| Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50 | 308615 50 |
| Special pull stud with internal thread suitable for steep tapers 50 | 308740 50 |
| Pull stud 90°sealed suitable for steep tapers 50 | 308795 50 |
| Pull stud 60°sealed suitable for steep tapers 50 | 308785 50 |
| Pull studForm B suitable for steep tapers 50 | 308640 50 |
| Wrench for pull studsISO 7388 suitable for ISO taper size 50 | 308830 50 |
| Pull studForm A suitable for steep tapers 50 | 308600 50 |