

Garant**Arbor for screw-in milling cutters with thread, SK 40, Thread M × Length L1:
M8X25****Order data**

Order number	301303 M8X25
GTIN	4062406105327
Item class	31A

Description**Version:**

Tapered design.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Technical description

External Ø D	15 mm
Overhang dimension A	44 mm
Thread M	M8x25
Ø D ₂	13 mm
L ₂	5 mm
Bore Ø D ₁ tolerance IT6	8.5 mm
Reach L ₁	25 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	ADB

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Threaded copy mill arbor

Accessories

ER chuck key for ER collet chuck 25	309680 25
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Torque wrench with reversible ratchet maximum torque 200 N·m	656050 200
ER chuck key 1/2 inch socket for ER collet chuck 40	309700 40
Pull stud Form B suitable for steep tapers 40	308640 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Wrench for ER Mini nuts for ER collet chuck 25	309740 25
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
Pull stud sealed suitable for steep tapers 40	308635 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud Form A suitable for steep tapers 40	308600 40
Pull stud sealed suitable for steep tapers 40	308660 40

Pull stud 90°sealed suitable for steep tapers 40	308790 40
ER chuck key for ER collet chuck 40	309680 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Torque insert for ER Mini nuts for ER collet chuck 25	309745 25
Pull studsealed, form B suitable for steep tapers 40	308650 40
ER chuck key1/2 inch socket for ER collet chuck 25	309700 25
Pull studMazak, form A suitable for steep tapers 40M	308670 40M