

Garant**Solid carbide HPC micro-drill, TiAlN, Ø DC +0.004: 2,45mm****Order data**

Order number	121220 2,45
GTIN	4045197353405
Item class	11E

Description**Version:**

High performance miniature drill **with extra long flutes.**

Shank Ø 3 h6 for shrink-fit chucks.

High concentricity, precision ground for **HPC applications in steel.**

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Number of cutting edges Z	2
Feed f in steel < 1100 N/mm ²	0.05 mm/rev.
Flute length L_c	15 mm
Nominal Ø D_c	2.45 mm
Shank tolerance	h6
Tolerance nominal Ø	0 / 0.004
Shank Ø D_s	3 mm
Overall length L	46 mm
Standard	Manufacturer's standard
recommended maximum drilling depth L_2	11.4 mm
Coating	TiAlN
Tool material	Solid carbide

Type	N
Point angle	130 degrees
Shank	Parallel shank to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	200 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	140 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	70 m/min	P
Steel < 900 N/mm ²	suitable	70 m/min	P
Steel < 1100 N/mm ²	suitable	55 m/min	P
Steel < 1400 N/mm ²	suitable	35 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	25 m/min	H
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable	30 m/min	M
Ti > 850 N/mm ²	suitable	20 m/min	S
GG(G)	suitable	90 m/min	K
CuZn	suitable	140 m/min	N
Uni	suitable		

wet maximum	suitable
dry	suitable only under restricted conditions