

**Garant**
**Special flap disc (ZA) with overlap between strips, 125 mm Ø, Grit: 80**

**Order data**

Order number	566295 80
GTIN	4045197720474
Item class	51M

**Description**
**Version:**

Flap disc with **extra large overlap between strips (10 mm)**. High metal removal rate and service life due to the use of high-quality **Zirconium Aluminium Oxide (ZA)** on robust mixed fabric. With active coating for cool cutting.

- **Dished shape – for dressing edges/welds and surface grinding with approach angles 15–25°.**

**Application:**

Ideal for grinding tasks alternating between **surface grinding and contour grinding** and for use in **inaccessible places** such as grinding out of weld fillets.

**Technical description**

Bore Ø	22.23 mm
Shape description	dished with overlap between strips
Grit	80
Disc Ø	125 mm

Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	125 mm Ø
optimised for material	Steel
optimised for material	INOX
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable only under restricted conditions		
dry	suitable		