


**Solid carbide milling cutter, TiAlN, Ø h10 DC: 12mm**

**Order data**

Order number	203520 12
GTIN	4045197119681
Item class	12X

**Description**
**Version:**

**High stability and extremely smooth cutting action due to at least 6 teeth.** Eccentric relief ground. **For profile milling as a finishing operation.**

**Technical description**

Corner chamfer width at 45°	0.1 mm
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.08 mm
Cutting edge Ø $D_c$	12 mm
No. of teeth Z	6
Shank Ø $D_s$	12 mm
Overall length L	83 mm
Flute length $L_c$	26 mm
Direction of infeed	horizontal
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	h10
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	Solid carbide

Standard	DIN 6527
Type	N
Cutting width $a_e$ for milling operation	$0.1 \times D$ for side milling
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	600 m/min	N
Alu > 10% Si	suitable only under restricted conditions	400 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	190 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	95 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	85 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M
GG(G)	suitable	120 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	Suitable only under restricted conditions		

