

Garant
Solid carbide milling cutter MTC, uncoated, Ø h6 DC: 5mm

Order data

Order number	202247 5
GTIN	4045197878854
Item class	11X

Description
Version:

Eccentric relief ground, additionally **polish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

Application:

Especially for **MTC (Multi Task Cutting)** use on the new generation of turning / milling centres.

Technical description

Overall length L	80 mm
Cutting edge Ø D _c	5 mm
Recess Ø D ₁	4.7 mm
Shank	DIN 6535 HA to h6
Flute length L _c	8 mm
Feed f _z for slot milling in short-chipping aluminium	0.015 mm
Direction of infeed	horizontal, oblique and vertical
Overhang length L ₁ incl. recess	30 mm
Shank Ø D _s	6 mm
Tolerance nominal Ø	h6
No. of teeth Z	3
Corner chamfer width at 45°	0.1 mm
Feed f _z for side milling in short-chipping aluminium	0.02 mm

Shank form	HA
Balance quality with shank	G 2.5 with HA
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	MTC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable	130 m/min	N
Aluminium (short chipping)	suitable	100 m/min	N
Alu > 10% Si	suitable	85 m/min	N
PMMA acrylic	suitable	140 m/min	N
PE-HD	Suitable	100 m/min	N
PA 66	Suitable	110 m/min	N
PEEK	suitable	100 m/min	N
PF 31	Suitable	85 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	100 m/min	N

Cu	Suitable	80 m/min	N
CuZn	Suitable	100 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		
Services			

Shank grinding Type HB

129100 HB