

**HOLEX****Abrasive sleeve holder slit, conical shank 6 mm Ø, largest Ø×head length:  
36X60mm**

## Order data

Order number	553830 36X60
GTIN	4045197722942
Item class	52E

## Description

**Version:**

Slotted, resilient rubber body with steel shank. Ground outer face for best concentricity.

## Technical description

maximum speed	13500 min <sup>-1</sup>
largest Ø	36 mm
smallest Ø	22 mm
Head Ø	5 mm
Head length	60 mm
Shape description	conical
Shank Ø	6 mm
Backing material	resilient rubber body
Type of product	Tool sleeve carrier