



Steep taper (SK) drill chuck arbor, SK / drill chuck taper: 40/16



Order data

Order number	342886 40/16
GTIN	4062406109370
Item class	32A

Description

Version:

Through hardened and ground. High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

High precision version with DIN taper shank and locking thread.

Application:

For mounting drill chucks on milling machines with DIN 2080 steep tapers. With internal locking thread M16 **and snap ring groove for automatic clamping** (e.g. Maho, Deckel, Mikron etc., also suitable for all standard machines **with manual clamping**).

Standard:

Bohrfutterkegel **DIN 238**.

Technical description

Taper \varnothing D	15.733 mm
Drill chuck taper DIN 238	B 16
Steep taper size	40
Internal pull thread	M16
Colour code for suitable shank	SK 40
Type of product	Drill chuck adapter

