

Garant
Short drill chuck Form E, HSK-E 40, Clamping range: 0,3-10mm

Order data

Order number	307681 0,3-10
GTIN	4062406115098
Item class	31B

Description
Version:

- **For clockwise and anticlockwise rotation.**
- **With RFID/Balluffchip bore.**

With through coolant feed up to max. 50 bar.

Concentricity $\leq 20 \mu\text{m}$. Concentricity $\leq 20 \mu\text{m}$.

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Socket wrench No. 309890. Coolant tube No. 309880.

Technical description

Clamping range	0.3 - 10 mm
External \varnothing D	38 mm
Type	slim
Spare chuck key No. 627425	4 AF
Overhang dimension A	91 mm
Adapter	HSK-E 40
Through-coolant	yes, with max. 50 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 20 μm
Type of product	Short drill chuck