



## Burr Z7 – medium, diamond cut, Carbide, Type: AS0820



### Order data

Order number	540750 AS0820
GTIN	4045197723468
Item class	52D

### Description

#### Version:

Shank Ø 6 mm.

**HOLEX** burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape (ZYAS), with end cut.**

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

### Technical description

Head Ø	8 mm
Toothing grit designation	medium
Type of cut	staggered teeth
Shape description	Cylindrical with end cut
Overall length	64 mm
Tooth type abbreviation	Z7
Shape	AS0820
Shank Ø	6 mm
Head length	19 mm
Series	#Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		