



## Mini burr Z7 – medium, diamond cut, Carbide, Type: H0613



### Order data

Order number	546910 H0613
GTIN	4045197724335
Item class	52D

### Description

#### Version:

**HOLEX** – burrs are manufactured from highest quality carbide with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank Ø 3 mm.

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

### Technical description

Head Ø	6 mm
Toothing grit designation	medium
Shape description	Flame
Tooth type abbreviation	Z7
Type of cut	staggered teeth
Overall length	43 mm
Shape	H0613
Shank Ø	3 mm
Head length	13 mm
Series	#Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		