

Garant
Clamping toolholder DCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 40/19mm

Order data

Order number	250017 40/19
GTIN	4062406119126
Item class	21T

Technical description

Overall length L	250 mm
Shim	259031 18
Clamp, screw, spring	259035 1
ISO code toolholder	DCLNR/L 4040S19
Functional width L ₄	50 mm
suitable indexable insert	CN.. 1906..
Insert size	19 mm
Head length L ₁	45 mm
Shank size	40 mm
Shim screw	259025 13
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 18	259031 18
Shim Type 36	259031 36
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2