

Garant
Machine tap for synchronised spindles HSS-E-PM IC / Form C, DLC, M: M5

Order data

Order number	134285 M5
GTIN	4045197649287
Item class	11H

Description
Version:

Sturdy version with right-hand helix and shank to DIN 1835-B. Special geometry for use on machines with **synchronised spindle drives**. The tap is controlled by the synchronising spindle of the machine. With the latest generation of special **DLC coating sp²** for optimum tool life. For use with **emulsion** (fat content minimum 8%).

With **internal coolant supply** for maximum tool life.

Note:

For use on synchronised spindles, the **GARANT** quick-change tapping chuck **No. 338100 – 338121 with minimum length adjustment (MLA)** ensures maximum process reliability.

Thread type: M

Tool material: HSS E PM

Standard: Manufacturer's standard

Tolerance class: ISO 2X 6HX

Thread pitch: 0.8 mm

Overall length L: 70 mm

Shank Ø D_s: 6 mm

Shank square □: 4.9 mm

Tapping hole Ø: 4.2 mm

Technical description

Tapping hole Ø	4.2 mm
Thread Ø	5 mm
Number of cutting edges Z	2
Thread pitch	0.8 mm

Number of clamping slots	2
Standard	Manufacturer's standard
Shank $\varnothing D_s$	6 mm
Overall length L	70 mm
Shank square \square	4.9 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Thread depth	12.5 mm
Thread type	M
Thread size	M5
Coating	DLC
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	DIN 1835 B to h6
Through-coolant	yes
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Shank tolerance	h6
Type of threading tool	Machine tap for synchronous machining
Colour ring	yellow
Type of product	Tap

User data

	Suitability	V_c	ISO code
Aluminium	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N

Alu > 10% Si	suitable	20 m/min	N
PMMA acrylic	suitable	25 m/min	N
PA 66 GF30	suitable only under restricted conditions	20 m/min	N
PTFE CF25	suitable	25 m/min	N
Cu	suitable	55 m/min	N
CuZn	suitable	35 m/min	N
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		