


Garant**Burr Z FINE – very fine, Carbide, Type: G0618****Order data**

| | |
|--------------|---------------|
| Order number | 540440 G0618 |
| GTIN | 4045197725783 |
| Item class | 51D |

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|--------------|
| Toothing grit designation | very fine |
| Tooth type abbreviation | Z FINE |
| Shape description | Pointed arch |
| Shape | G0618 |
| Head Ø | 6 mm |
| Overall length | 50 mm |
| Shank Ø | 6 mm |
| Head length | 18 mm |

| | |
|-----------------|----------------------------|
| Series | Tooth configuration Z FINE |
| Tool material | Carbide |
| Type of product | Burr |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|--------------------|----------------------|-----------------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |