



Hacksaw frame with bimetal blade 24 teeth, Blade length: 300mm



Order data

Order number	580750 300
GTIN	4062406128579
Item class	52S

Description

Version:

Sturdy hacksaw frame with die-cast aluminium components. **Very high blade tension** up to 1500 N is easily achieved using the tensioning nut incorporated in the handle. **Alternative blade setting at 40° for flush cutting.** Additional saw blades can be stored in the handle. Overall length 405 mm.

Frame height 110 mm.

The bow saw with its prominent bow frame is characterised by the u-shaped bow which tensions the saw blades. The limitation in depth of cut of hand bow saws is presented by the distance from the blade to the bow. This frame shape permits the use of particularly slim saw blades, which in other frame shapes would be liable to buckle when subjected to cutting movements with the force in alternate senses or other than in the pulling sense. Thanks to the thin hacksaw blades the metal cutting effort required is reduced, because of the small cutting width. Thus this type of saw is the classic standard for hacksaw work in metalworking.

Supplied with:

HOLEX bimetal hacksaw blade No. 582970.

Technical description

TPI	24
Blade length	300 mm
Type of product	Hacksaw frame

Accessories

Hacksaw blade, single-sidedbimetal

582970