

**Jobber drill HSS N, TiN, Ø DC h8: 4,4mm****Order data**

Order number	114360 4,4
GTIN	4045197016508
Item class	12B

Description**Version:**

Standard core without core taper.

Precision ground point.

Profile ground:

High concentricity and pitch accuracy, drills for series production use.

With point geometry shape C from size 2.4 mm

Recommendation:**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c$$

Technical description

Flute length L_c	47 mm
Nominal $\varnothing D_c$	4.4 mm
Number of cutting edges Z	2
Feed f in steel $< 500 \text{ N/mm}^2$	0.09 mm/rev.
Tolerance nominal $\varnothing$	h8
Shank $\varnothing D_s$	4.4 mm
Overall length L	80 mm
Standard	DIN 338
recommended maximum drilling depth L_2	40.4 mm
Point angle	118 degrees

Shank	Plain shank
Coating	TiN
Tool material	HSS
Type	N
Helix angle	35-40 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	56 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm ²	suitable	50 m/min	P
Steel < 750 N/mm ²	suitable	37 m/min	P
Steel < 900 N/mm ²	suitable	31 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	12 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	10 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	15 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	10 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	6 m/min	S
GG(G)	suitable	31 m/min	K
CuZn	suitable only under restricted conditions	80 m/min	N

Oil	suitable
wet maximum	suitable