

Garant
GARANT Master Alu PickPocket solid carbide roughing end mill HPC, uncoated, Ø e8 DC: 16mm

Order data

Order number	202012 16
GTIN	4062406126315
Item class	11X

Description
Version:

For roughing and finishing.

Up to 2×D into solid material at very high feed rates and smooth cutting action.

Very high feed rates when plunging vertically.

Ramping capability up to 45°.

Advantage:

Optimised flute form, eccentric relief ground, generous chip spaces.

Note:

A minimum oversize of 0.1×D must be maintained for subsequent finishing operations.

Technical description

Balance quality with shank	G 2.5 with HA
Overhang length L ₁ incl. recess	58 mm
Feed f _z for slot milling in short-chipping aluminium	0.12 mm
Shank Ø D _s	16 mm
Direction of infeed	horizontal, oblique and vertical
Cutting edge Ø D _c	16 mm
No. of teeth Z	3
Tolerance nominal Ø	e8
Recess Ø D ₁	15.8 mm

Feed f_z for side milling in short-chipping aluminium	0.14 mm
Overall length L	108 mm
Helix angle	42 degrees
Shank	DIN 6535 HA to h6
Flute length L_c	31 mm
Corner chamfer angle	90 degrees
Series	Master Alu
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	250 m/min	N
Aluminium (short chipping)	suitable	200 m/min	N
Alu > 10% Si	suitable	180 m/min	N
PMMA acrylic	Suitable	180 m/min	N
PE-HD	Suitable	130 m/min	N
PA 66	Suitable	150 m/min	N

PEEK	Suitable	130 m/min	N
PF 31	Suitable	110 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	180 m/min	N
Cu	Suitable	120 m/min	N
CuZn	Suitable	150 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable		

Services

Shank grinding Type HB

129100 HB