

Garant
Solid carbide jobber drill, TiAlN, Ø DC h7: 1,5mm

Order data

Order number	122251 1,5
GTIN	4045197748942
Item class	11E

Description
Version:
Similar to DIN 338.

Nominal Ø and shank Ø equal.

TiAlN coating for even better performance.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Non slip clamping in drill chuck No. 341050 with diamond coated jaws.

Through-coolant: no

Standard: DIN 338

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 15.8 mm

Tolerance nominal Ø: h7

Overall length L: 40 mm

Shank Ø D_s : 1.5 mm

Feed f in steel < 1100 N/mm²: 0.03 mm/rev.

Technical description

Shank Ø D_s	1.5 mm
Feed f in steel < 1100 N/mm ²	0.03 mm/rev.
Tolerance nominal Ø	h7
Shank tolerance	h7
Flute length L_c	18 mm
Nominal Ø D_c	1.5 mm

Standard	DIN 338
Number of cutting edges Z	2
Overall length L	40 mm
recommended maximum drilling depth L ₂	15.8 mm
Coating	TiAlN
Tool material	solid carbide
Type	N
Point angle	118 °
Helix angle	30 °
Shank	Parallel shank to h7
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	260 m/min	N
Aluminium (short chipping)	suitable	180 m/min	N
Alu > 10% Si	suitable	180 m/min	N
Steel < 500 N/mm ²	suitable	90 m/min	P
Steel < 750 N/mm ²	suitable	90 m/min	P
Steel < 900 N/mm ²	suitable	80 m/min	P
Steel < 1100 N/mm ²	suitable	60 m/min	P
Steel < 1400 N/mm ²	suitable	35 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable	25 m/min	M
Ti > 850 N/mm ²	suitable	25 m/min	S

GG(G)	suitable	90 m/min	K
CuZn	suitable	180 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		