


**Marker, Shank Ø d: 12mm**

**Order data**

Order number	358740 12
GTIN	4045197707482
Item class	32B

**Description**
**Version:**

Body of aluminium with Weldon shank. Stepless adjustment of the pre-load force. Character depth 0.1 - 0.3 mm.

**Advantage:**

Surface sealing without weakening or damaging the material. Inscription speed corresponds to the maximum feed rate. High wear resistance, with long working life for the special needles. Suitable for inscriptions on round surfaces. Can be used on the lathe. High process reliability. Needles easily withdrawn, therefore **quick needle change**. Irregularities up to 7 mm in the workpiece surface (depending on profile) can be compensated.

**Application:**

For marking on a wide variety of materials such as aluminium, titanium, steel, bronze, copper, brass, plastics etc. Smaller needle tips allow inscriptions on harder surfaces up to 57 HRC.

**Supplied with:**

size 12 – including **3 needles** No. 358745 size 0.3 – 0.5 – 0.8.

Size 20 –including **3 needles** No. 358745 size 0.3 – 0.6 – 1.0.

**Technical description**

L	66 mm
Shank Ø d	12 mm
Ø D <sub>1</sub>	3 mm
Type of product	Labelling tool

## Accessories

Spare needle Radius 0,6 mm	358745 0,6
Spare needle Radius 1,0 mm	358745 1,0
Spare needle Radius 0,3 mm	358745 0,3
Spare needle Radius 0,5 mm	358745 0,5
Spare needle Radius 0,8 mm	358745 0,8