

Garant**Drill chuck with straight shank, Type: 32****Order data**

Order number	341265 32
GTIN	4062406086633
Item class	31B

Description**Version:**

- For clockwise and anticlockwise rotation.
- Slim design.
- Targeted delivery of coolant.

Advantage:

- Very flexible applications due to the plain shank.
- Optimum holding torques at the tool.

Supplied with:

Torx chuck key with T-handle.

Technical description

Drill head length open	81.9 mm
Clamping range	1 - 16 mm
External Ø	50 mm
Drill head length closed	92 mm
Shaft length	60 mm
Overall length	141.9 mm
Shank Ø D _s	32 mm
Concentricity	≤ 20 µm
Balance quality G at rotational speed	G 6.3 at 15,000 rpm

Through-coolant	yes, with max. 50 bar
Type of product	Drill chuck