


Solid carbide slot drill, uncoated, Ø e8 DC: 8 mm

Order data

Order number	202241 8
GTIN	4045197767042
Item class	12X

Description
Version:

Eccentric relief ground, additionally **finish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

Application:

For roughing and finishing.

Through-coolant: no

Tolerance nominal Ø: e8

No. of teeth Z: 3

Helix angle: 45 degrees

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HA to h6

No. of teeth Z: 3

Flute length L_c : 16 mm

Overall length L: 63 mm

Shank Ø D_s : 8 mm

Feed f_z for slot milling in short-chipping aluminium: 0.03 mm

Feed f_z for side milling in short-chipping aluminium: 0.04 mm

Technical description

No. of teeth Z	3
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA to h6
Feed f_z for slot milling in short-chipping aluminium	0.03 mm
Tolerance nominal Ø	e8

Shank $\varnothing D_s$	8 mm
Overall length L	63 mm
Feed f_z for side milling in short-chipping aluminium	0.04 mm
Flute length L_c	16 mm
Cutting edge $\varnothing D_c$	8 mm
Helix angle	45 degrees
Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	yellow
Type of product	End mill

Services

Shank grinding Type HB	129100 HB
------------------------	-----------