


**Garant****Manual vice for drilling machines, Jaw width A: 60mm****Order data**

Order number	365035 60
GTIN	4045197770677
Item class	31S

**Description****Version:**

- **Sturdy design with strong spindle.**
- **Jaws through hardened and ground.**
- **Precise clamping due to long flat guide.**
- **One jaw with horizontal and vertical prismatic profiles for round material, one jaw smooth.**
- **Both jaws are stepped at the top to clamp flat parts.**
- **Patent-pending integrated eccentric quick clamping for a secure grip on the drilling machine table.**
- **The quick clamping in the area of the grooves makes it possible to process the clamped workpiece flexibly and efficiently at any desired position on the entire drilling machine table without re-clamping.**

**Application:**

For clamping components on drilling machines.

**Material:**

Body and movable jaw made of special cast iron.

**Accuracy:**

Within **0.10 mm**.

**Technical description**

Clamping range b	79 mm
Clamping slot spacing	90 mm

Overall height c	55 mm
Base body width B	115 mm
maximum overall length L <sub>4</sub>	271 mm
Base body length a	169 mm
Colour code for suitable accessories	BM vice, blue
Jaw width A	60 mm
Clamping slot width	13 mm
Jaw height C	25 mm
Weight	3.2 kg
Type of product	Drilling machine vice

## Accessories

Pair of spare jaws (2 pieces) for quick-release vice or drilling machine vice for type 60	365036 60
Slide for No. 365023	365025
Backstop Type 1	365028 1
Spare spindle for drilling machine manual vice for type 60	365037 60