

Garant

Carbide boring bar E.. SVUBL 93°, for indexable inserts VB., left-hand, Shank Ø / insert size: 16/11mm


Order data

Order number	261119 16/11
GTIN	4062406099831
Item class	21T

Technical description

Setting angle κ	93 degrees
Pack of insert screws	269028 7
Overall length L	200 mm
ISO code toolholder	E16R SVUBR/L 11
Head length L_1	16.5 mm
Centre offset L_3	11 mm
Minimum pre-drill $\varnothing D_{\min}$	21 mm
Insert size	11 mm
Clamping height L_2	15 mm
suitable indexable insert	VB.. 1103..
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar