

**Garant**

**Carbide boring bar E.. SVJCR 142°, for indexable inserts VC.., right-hand,  
Shank Ø / insert size: 16/11mm**


**Order data**

Order number	261326 16/11
GTIN	4062406100490
Item class	21T

**Technical description**

Centre offset $L_3$	2 mm
Pack of insert screws	269028 27
Clamping height $L_2$	15 mm
Insert size	11 mm
ISO code toolholder	E16R SVJCR/L11
Neck width $L_4$	9.5 mm
Setting angle $\kappa$	142 degrees
Head length $L_1$	31.4 mm
Overall length $L$	200 mm
suitable indexable insert	VC.. 1103..
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar