



## Manual vice for drilling machines, Jaw width A: 80mm



### Order data

Order number	365045 80
GTIN	4045197771018
Item class	32D

### Description

#### Version:

- **Sturdy and handy design.**
- **Jaws through hardened and ground.**
- **Consistent overall length (the spindle retracts into the handle)**
- **Universal fastening capability due to long holes.**
- **Movable jaw with guides at the sides.**
- **Fixed jaw with three vertical prismatic and one horizontal prismatic section.**

#### Application:

For clamping components on drilling machines.

#### Material:

**Cast iron body.**

#### Accuracy:

Within **0.20 mm.**

### Technical description

Jaw height C	30 mm
Overall height c	64 mm
Weight	4 kg
Clamping range b	65 mm

Base body length a	233 mm
Jaw width A	80 mm
Type of product	Drilling machine vice

---

## Accessories

Pair of spare jaws (2 pieces) for manual vice for drilling machines for type 80	365046 80
---	-----------