

**Garant**

**Carbide boring bar E.. SVJCR 142°, for indexable inserts VC.., right-hand,  
Shank Ø / insert size: 10/07mm**


**Order data**

Order number	261326 10/07
GTIN	4062406100421
Item class	21T

**Technical description**

Overall length L	125 mm
Minimum pre-drill Ø $D_{min}$	13 mm
ISO code toolholder	E10K SVJCR/L07
Setting angle $\kappa$	142 degrees
Neck width $L_4$	6.3 mm
Pack of insert screws	269028 27
Head length $L_1$	18 mm
Clamping height $L_2$	9 mm
suitable indexable insert	VC.. 0702..
Centre offset $L_3$	1.5 mm
Insert size	7 mm
Shank Ø $D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar