

Garant

Carbide boring bar E.. SVJCL 142°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 8/05mm


Order data

Order number	261327 8/05
GTIN	4062406100575
Item class	21T

Technical description

Insert size	5 mm
Neck width L ₄	6 mm
ISO code toolholder	E08F SVJCR/L05
Centre offset L ₃	3 mm
Pack of insert screws	269028 26
Clamping height L ₂	7.5 mm
Minimum pre-drill Ø D _{min}	8 mm
Overall length L	80 mm
Head length L ₁	26 mm
Setting angle κ	142 degrees
suitable indexable insert	VC.. 0501..
Shank Ø D _s	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar