

**Garant**
**Clamping toolholder DCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 32/16mm**

**Order data**

Order number	250017 32/16
GTIN	4045197771988
Item class	21T

**Technical description**

Shank size	32 mm
Shim	259031 35
suitable indexable insert	CN.. 1606..
Clamp, screw, spring	259035 6
Overall length L	170 mm
Shim screw	259025 11
Head length L <sub>1</sub>	40 mm
Functional width L <sub>4</sub>	40 mm
ISO code toolholder	DCLNR/L 3232P16
Insert size	16 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim screw Type 11	259025 11
Shim Type 35	259031 35
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX25	674248 TX25