

Garant

Carbide boring bar E.. SVJCL 142°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 16/11mm


Order data

| | |
|--------------|---------------|
| Order number | 261327 16/11 |
| GTIN | 4062406100650 |
| Item class | 21T |

Technical description

| | |
|-------------------------------|----------------|
| Minimum pre-drill Ø D_{min} | 22 mm |
| suitable indexable insert | VC.. 1103.. |
| Pack of insert screws | 269028 27 |
| Overall length L | 200 mm |
| Centre offset L_3 | 2 mm |
| Insert size | 11 mm |
| Setting angle κ | 142 degrees |
| Head length L_1 | 31.4 mm |
| ISO code toolholder | E16R SVJCR/L11 |
| Neck width L_4 | 9.5 mm |
| Clamping height L_2 | 15 mm |
| Shank Ø D_s | 16 mm |
| Standard | Works standard |
| Application type | left-hand |
| Boring depth up to | 8×D |
| Tool material | Carbide |

| | |
|-----------------|-------------------------------|
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring Bar |