

Garant

**Clamping toolholder SCRCR 75°, for indexable inserts CC., right-hand,
Shank / insert size: 12/09mm**



Order data

Order number	260004 12/09
GTIN	4045197772497
Item class	21T

Technical description

Head length L ₁	15 mm
Shank size	12 mm
Pack of insert screws	269028 8
Overall length L	80 mm
suitable indexable insert	CC.. 09T3..
Insert size	9 mm
Functional width L ₄	13 mm
ISO code toolholder	SCRCR/L 1212F09
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15