

Garant

Clamping toolholder SCRCL 75°, for indexable inserts CC., left-hand, Shank / insert size: 12/09mm



Order data

Order number	260005 12/09
GTIN	4045197772572
Item class	21T

Technical description

Functional width L ₄	13 mm
Shank size	12 mm
suitable indexable insert	CC.. 09T3..
Pack of insert screws	269028 8
Overall length L	80 mm
Insert size	9 mm
ISO code toolholder	SCRCL/L 1212F09
Head length L ₁	15 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15