

Garant

Carbide boring bar E.. SVUCL 93°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 25/11mm


Order data

Order number	261329 25/11
GTIN	4062406100841
Item class	21T

Technical description

Head length L_1	23 mm
Setting angle κ	93 degrees
Overall length L	250 mm
suitable indexable insert	VC.. 1103..
ISO code toolholder	E25S SVUCR/L11
Insert size	11 mm
Centre offset L_3	17 mm
Minimum pre-drill $\varnothing D_{\min}$	31.5 mm
Clamping height L_2	23 mm
Pack of insert screws	269028 7
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar