

**Garant**

**Carbide boring bar E.. SVUCL 93°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 16/11mm**


**Order data**

Order number	261329 16/11
GTIN	4062406100827
Item class	21T

**Technical description**

Head length $L_1$	16.5 mm
Clamping height $L_2$	15 mm
Insert size	11 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	21 mm
suitable indexable insert	VC.. 1103..
Setting angle $\kappa$	93 degrees
Overall length $L$	200 mm
Centre offset $L_3$	11 mm
ISO code toolholder	E16R SVUCR/L11
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar