



Face mill arbor Form A, BT 40 short, Spigot \varnothing d1: 27mm



Order data

Order number	303017 27
GTIN	4062406101220
Item class	32A

Description

Version:

Taper shank, spigots, and contact surfaces ground on collar.
All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm. Form A.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Technical description

Spare milling cutter lock screw No. 309860 / 309861	27
External \varnothing D	50 mm
Suitable toggle spanner No. 309840	27
Overhang dimension A	35 mm
Spigot \varnothing d ₁	27 mm
Clamping \varnothing D ₁	27 mm
Adapter	BT 40 short
Standard	DIN 6357
Arbor standard	JIS B6339

Arbor standard	JIS B6339
Shape	A
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	≤ 5 μm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40