

**Face mill arbor Form A, BT 50 A = 100, Spigot Ø d1: 22mm****Order data**

Order number	303037 22
GTIN	4062406101251
Item class	32A

Description**Version:**

Taper shank, spigots, and contact surfaces ground on collar.

All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm. Form A.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Technical description

Suitable toggle spanner No. 309840	22
Overhang dimension A	100 mm
External Ø D	48 mm
Spigot Ø d ₁	22 mm
Spare milling cutter lock screw No. 309860 / 309861	22
Clamping Ø D ₁	22 mm
Adapter	BT 50 A = 100
Standard	DIN 6357
Arbor standard	JIS B6339

Arbor standard	ISO 7388-2
Shape	A
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor