

Garant**Clamping toolholder SCACR 90°, for indexable inserts CC., right-hand,
Shank / insert size: 10/06mm****Order data**

Order number	260014 10/06
GTIN	4045197797537
Item class	21T

Technical description

Insert size	6 mm
Functional width L ₄	10 mm
ISO code toolholder	SCACR/L 1010M06
Overall length L	150 mm
Head length L ₁	10 mm
Shank size	10 mm
suitable indexable insert	CC.. 0602..
Pack of insert screws	269021 1
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7