

**Garant**

**Clamping toolholder SCACR 90°, for indexable inserts CC., right-hand,  
Shank / insert size: 16/06mm**



### Order data

Order number	260014 16/06
GTIN	4045197797551
Item class	21T

### Technical description

Head length $L_1$	16 mm
Shank size	16 mm
Functional width $L_4$	16 mm
suitable indexable insert	CC.. 0602..
Insert size	6 mm
Pack of insert screws	269021 1
Overall length L	150 mm
ISO code toolholder	SCACR/L 1616M06
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7