

Garant**Synchro tool head for ER16, Tap shank \varnothing d₂: 5mm****Order data**

Order number	338183 5
GTIN	4062406102067
Item class	31P

Description**Version:**

- **Tapping and thread forming on machines with synchronised spindles.**
- **Minimum Length Adjustment: +0.5mm / -0.2 mm.**
- **Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.**
- **For collet chucks and driven tools to ISO 15488 (DIN 6499).**
- **Suitable for left-hand and right-hand threads.**

Suitable for:

ER synchro collet No. 338180.

Technical description

Overhang L ₁	24 mm
Shank square	4 mm
for tap shank \varnothing d ₂ DIN 374/376	M5
for tap shank \varnothing d ₂ DIN 371	M4
\varnothing D ₂	12.7 mm
Through-coolant	yes, with max. 50 bar
Type of product	Tapping adapter

