



## Steep taper (SK) drill chuck arbor, SK / drill chuck taper: 50/16



### Order data

Order number	342887 50/16
GTIN	4062406109394
Item class	32A

### Description

#### Version:

**Through hardened and ground.** High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

High precision version with DIN taper shank and locking thread.

**Steep taper to DIN 69871 A, Part 1** with tool changer flange and thread for pull stud.

#### Application:

For mounting drill chucks on milling machines with DIN 2080 steep tapers.

#### Standard:

Bohrfutterkegel **DIN 238**.

### Technical description

Steep taper size	50
Drill chuck taper DIN 238	B 16
Colour code for suitable shank	SK 50
Internal pull thread	M24
Taper $\varnothing$ D	15.733 mm
Type of product	Drill chuck adapter

