

Garant

Clamping toolholder SCACL 90°, for indexable inserts CC., left-hand, Shank / insert size: 12/09mm



Order data

Order number	260015 12/09
GTIN	4045197797827
Item class	21T

Technical description

suitable indexable insert	CC.. 09T3..
Insert size	9 mm
ISO code toolholder	SCACR/L 1212M09
Head length L ₁	12 mm
Pack of insert screws	269021 2
Shank size	12 mm
Overall length L	150 mm
Functional width L ₄	12 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 2	269021 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15