

**Garant**
**Clamping toolholder SDACR 90°, for indexable inserts DC., right-hand,  
Shank / insert size: 12/07mm**

**Order data**

Order number	260298 12/07
GTIN	4045197797865
Item class	21T

**Technical description**

suitable indexable insert	DC.. 0702..
ISO code toolholder	SDACR/L 1212M07
Overall length L	150 mm
Pack of insert screws	269021 1
Insert size	7 mm
Shank size	12 mm
Functional width L <sub>4</sub>	12 mm
Head length L <sub>1</sub>	15 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7