

Garant**Clamping toolholder SDACR 90°, for indexable inserts DC., right-hand,
Shank / insert size: 16/11mm****Order data**

Order number	260298 16/11
GTIN	4045197797896
Item class	21T

Technical description

Shank size	16 mm
Head length L ₁	20 mm
Functional width L ₄	16 mm
Overall length L	150 mm
ISO code toolholder	SDACR/L 1616M11
Insert size	11 mm
suitable indexable insert	DC.. 11T3..
Pack of insert screws	269021 2
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 2	269021 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15