

Garant
Clamping toolholder SDACL 90°, for indexable inserts DC., left-hand, Shank / insert size: 16/07mm

Order data

Order number	260299 16/07
GTIN	4045197797933
Item class	21T

Technical description

Functional width L_4	16 mm
Shank size	16 mm
Insert size	7 mm
Pack of insert screws	269021 1
suitable indexable insert	DC.. 0702..
Overall length L	150 mm
ISO code toolholder	SDACR/L 1616M07
Head length L_1	16 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7