

Garant

Clamping toolholder SDNCN 62,5°, for indexable inserts DC., neutral, Shank / insert size: 10/07mm



Order data

Order number	260301 10/07
GTIN	4045197797964
Item class	21T

Technical description

Insert size	7 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	SDNCN 1010M07
Pack of insert screws	269021 1
Overhang L ₁ neutral holders	15 mm
Functional width L ₄ neutral holders	5.2 mm
Shank size	10 mm
Overall length L neutral holders	150 mm
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	62.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7