



Burr Z7 – medium, diamond cut, Carbide, Type: C1625



Order data

| | |
|--------------|---------------|
| Order number | 540750 C1625 |
| GTIN | 4045197723543 |
| Item class | 52D |

Description

Version:

Shank Ø 6 mm.

HOLEX burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|-------------------------|
| Toothing grit designation | medium |
| Shape | C1625 |
| Overall length | 70 mm |
| Tooth type abbreviation | Z7 |
| Shape description | ball nose |
| Type of cut | staggered teeth |
| Head Ø | 16 mm |
| Shank Ø | 6 mm |
| Head length | 25 mm |
| Series | #Tooth configuration Z7 |

| | |
|-----------------|---------|
| Tool material | Carbide |
| Type of product | Burr |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|----------------------|-----------------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| Uni | suitable | | |