

Garant
Clamping toolholder STJCR 93°, for indexable inserts TC., right-hand, Shank / insert size: 10/11mm

Order data

Order number	260904 10/11
GTIN	4045197798008
Item class	21T

Technical description

Shank size	10 mm
Insert size	11 mm
suitable indexable insert	TC.. 1102..
ISO code toolholder	STJCR/L 1010M11
Overall length L	150 mm
Pack of insert screws	269021 1
Head length L ₁	16 mm
Functional width L ₄	10 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7