

HOLEX
Burr Z7 – medium, diamond cut, Carbide, Type: D1614

Order data

Order number	540750 D1614
GTIN	4045197723598
Item class	52D

Description
Version:

Shank Ø 6 mm.

HOLEX burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Ball shape** (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape description	Ball
Toothing grit designation	medium
Shape	D1614
Type of cut	staggered teeth
Head Ø	16 mm
Overall length	60 mm
Tooth type abbreviation	Z7
Shank Ø	6 mm
Head length	14 mm

Series	#Tooth configuration Z7
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		