

**Garant**

**Clamping toolholder SVACL 90°, for indexable inserts VC.., left-hand, Shank / insert size: 12/16mm**



## Order data

|              |               |
|--------------|---------------|
| Order number | 261315 12/16  |
| GTIN         | 4045197798169 |
| Item class   | 21T           |

## Technical description

|                                 |                               |
|---------------------------------|-------------------------------|
| Overall length L                | 150 mm                        |
| suitable indexable insert       | VC.. 1604..                   |
| Shank size                      | 12 mm                         |
| Insert size                     | 16 mm                         |
| ISO code toolholder             | SVACR/L 1212M16               |
| Functional width L <sub>4</sub> | 12 mm                         |
| Head length L <sub>1</sub>      | 40 mm                         |
| Pack of insert screws           | 269021 2                      |
| Standard                        | Works standard                |
| Application type                | left-hand                     |
| Through-coolant                 | no                            |
| Setting angle κ                 | 90 degrees                    |
| Application                     | External longitudinal turning |
| Application                     | External longitudinal turning |
| Type of product                 | Boring bar                    |

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15