




Flap wheel (A), 120 grit, Head Ø×head width: 3/30X10 mm



Order data

Order number	554300 3/30X10
GTIN	4045197803337
Item class	52E

Description

Version:

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Grinding medium code: A

Shank Ø: 3 mm

recommended speed: 16000 rpm

maximum speed: 18000 rpm

Technical description

Grit	120
maximum speed	18000 rpm
Shank Ø	3 mm
Head Ø	30 mm
recommended speed	16000 rpm
Head width	10 mm
Grinding media	Aluminium Oxide grit (A)

Grinding medium code	A
Product name attribute	120 grit
Type of product	Flap wheel